



## Coating Machine (Experimental Type) CW-COT



### Feature:

Film Coating is used in Pharmaceutical, Food, Seed coating.

Follow the regulation of cGMP, PIC/S, GMP.

It's completed under full-closure and negative pressure drying during the coating process.


Punched hole of a coating pan design, high drying efficiency.

The process of operation is all digitized, easy for training operator.

The special bowl and baffle are designed without sharp angles or dead corners to apply even coloring with small weight deviation, features high coating speed, simple processing, short time, high efficiency, and polishing shiny.

Can in accordance with raw materials characteristic or special process requirements, it can input many different group of process parameter; After the conditions are all set up, it can do full-automatic procedure control.

## Line Graph:



## Specification:

Model CW-COT		Unit	COT-03	COT-05
Working Capacity		Kg/Batch	2~3	3~5
Heater		Kw	7	7
Pan Speed		Rpm	10~30	10~30
Pan Drive Motor		Kw	0.375	0.375
Pan Diameter		mm	450	450
Blower		Kw	2.25	2.25
Weight	Pressure	Kg	200	200
Dimensions	W	mm	1200	1200
	D		800	800
	H		1500	1500