

CARMAPHARM

Capsule Polishing Sorting Machine



It is a kind of capsule polished equipment with selecting function, it is not only used in capsule polishing and static eliminating, but also separating the qualified products from defected products automatically, it is suitable for all kinds of capsule. No need to replace its mould.

Traits:

The performance of machine is greatly excellent, the whole machine adopts stainless steel to be made, the selecting brush adopts fulling connection with fast speed, convenience of dismantling, cleaning thoroughly, the rotation speed of motor is controlled by converter, it can bear great starting pressure with steady running, its socket is equipped with rolling device with flexible operation and high efficiency as well high purity of polishing. It can automatically sort out capsules with low weight, empty body or scratches.

Technical Specification:

| | |
|-----------------------|--------------------------------|
| Production efficiency | 70000 capsules/min. |
| Capsule size | 00# 0# 1# 2# 3# 4# |
| Power | 220V 50Hz/110V 60Hz |
| Weight | 65kg |
| Total Power | 0.18KW |
| Vacuum dust-intake | 2.7m ³ /min |
| Compressed Air | 0.25m ³ /min 0.3Mpa |
| Overall Dimensions | 900*600*1100mm(L*W*H) |