



DGF 16/24 Model Oral Liquid Filling and Capping Machine



Main application:

The machine is suitable for food, chemical and pharmaceutical industries of small doses of tincture, of water of the filling and rolling cover. Can be done automatically lose bottle, measuring, filling, Daniel, wear cover, rolling cover, the working procedure such as a bottle.

Performance characteristics:

- Unscramble bottle directly into the bottle with disc big dial the roulette connect, unscramble bottle, lose smooth bottle.
- Tracking defoaming filling, no bubbles, measuring time.
- Lack of bottle filling, don't wear not caps, rolling cover.
- DuoTou shaft tilting single-blade rolling cover, sealing LaoShi, beautiful.
- "Bottle and pressure head synchronization, turn to the bottle not slippage.
- Imported PLC control, a high degree of automation. Touch screen operation panel, convenient, beautiful.
- Stepless speed regulation.

Technical parameters:

- Production capacity: 100-400 bottles/points
- Applicable specifications: 5-20 ml
- This needle. 16: filling
- Rolling a covering several: 24 head (24) per head
- Measurement error: more than plus or minus 1%
- Close case rate: 99% acuity
- Electricity let quantity: 2 Kw
- Shape dimension: 2345×1030×1570 mm (long×wide×high)
- The machine net weight: 1350 Kg