

Ultrasonic Washing Machine CX-CXP



This machine is mainly suitable for 20-500ml shoulder all kinds of round bottles or special-shaped bottle to bottle cleaning inside and outside, by two in water (tap water and ionized water, no oil compressed air) alternate irrigation. The bottle meet production process requirements, and the initial dry bottle, etc. This machine can be wired or standalone use. This equipment is fully in line with the new version of GMP requirements

Feature

1. Unique structure is compact, reasonable cleaning process
2. After washing the bottles spotlessness. Less water consumption, simple operation, easy maintenance
3. Appearance material adopts SUS304 stainless steel, easy to maintain
4. Optional: water cyclic utilization device
5. This equipment is fully in line with the new version of GMP requirements

Technical parameter:

| | |
|---------------------|---------------------------|
| Applied Bottles | 20-500ml |
| Productive Capacity | ≤20-100bottles/minute |
| Power Supply | 380V 50HZ |
| Power | 1.5KW |
| Water Consumption | 0.6-1t/h |
| Compressed Air | 15m³/h 0.3-0.4kg/cm² |
| Net Weight | 500kg |
| Dimension | 1200(L)×1100(W)×1200(H)mm |