

Lifting Device YS-LS-series



Function

- . For Fluid bed dryer/granulator discharge use.
- . For drums lifting and feeding.
- . For feeding into tablet pressing machine, capsule filling machine, coating machine, etc.

Theory

- . Lift: lifting drums by hydraulic cylinder can be positioned automatically.
- . Flip: Can be rotated by reducer, and can be 180° positioned automatically.
- . Machine platform rotation: Can be 90° rotated manually.


Application

Pharmaceutical, cosmetic, agriculture, health food or bio-tech products.

Feature

- . Let powder, granule, and tablet feeding automatically.
- . Operation by wire, easy to use and clean.
- . Closed operation, reduce dust.
- . Can be connected with cone mill, save manpower.

Flowchart (Click to see larger image)



Specification

Model	Angle	Rotating	Lifting Capacity (kg)	Lifting Height (mm)
YS-LS-60	180°	90	60	1200~2000
YS-LS-100	180°	90	100	1200~2000
YS-LS-150	180°	90	150	1300~2000
YS-LS-200	180°	90	200	1400~2000
YS-LS-300	180°	90	300	1500~2000