


Desiccant Sachet Inserter CPGZ-160



The machine is used for filling Unit Desiccant Sachet into containers which prevents tablets or capsules humidity. The machine adopts slip track to infeed the desiccant ribbon into the cutting zone. Two blades cut one piece of desiccant sachet from the ribbon and the sachet falls into the container exactly. It is designed strictly according to pharmaceutical GMP standard and technological requirements. The whole machine's running is quite simple and equips with the automatic stop system for absent and jammed bottle, automatic running with bottle infeed. In addition, wide range of applications in different size or shape bottles without spare parts changing over.

Technical Parameters

Model	CPGZ-160
Output	20- 130 Bottles/Min
Bottle size	15-300ML
Voltage	220V 50/60Hz Single Phase
Power	0.5 kW
Air Consumption	0.4 MPa / 0.3 m3/h
Overall Dimension	1600 (L)×750 (W)×1800 (H) mm
Weight	280 kg