


6 Needles Ampoules Filling and Sealing Machine



Introduction:

- 1. Applicable to the drawing of the ampoule filling and sealing of the pharmaceutical factory.
- 2. This machine is a 6-station stepping transmission system. Each time, 6 bottles are used as a group, which are sent to each process point to complete the bottle feeding.
- 3. The former is filled with nitrogen, filled with medicine, and then filled. Nitrogen, preheating, wire drawing and other processes.
- 4. With an oxy-hydrogen generator, the interface is perfectly matched. The drive rack is stainless steel and the pressure bottle plug fits tightly. See the product manual for the random accessories and configuration table.

Features:

- The transmission cam of the machine is a steel casting, which is not easy to wear. The rotating cam is guaranteed for 2 years, and there is wear in 2 years. The manufacturer is responsible for replacement.
- Performance test and acceptance method: according to the factory standard test.

Main Parameter

| Name | 6 needles ampoules filing and sealing machine |
|---------------------|---|
| Model | ALG- 5ml |
| | (with 1-3ml) |
| Producing capacity | 9000-12000pcs/h |
| Total motor power | 0.55KW |
| Matrial | Stainless steel (304) |
| Overall size | 1950×950×1300mm |
| Motor | M28014/380V |
| Gearbox | WCH |
| Frequency converter | 0.75 |