

## *GG-118(P5) Ampoule Oral Liquid Filling Sealing Machine with PM-100 Labeling Machine*



### **Performance and feature**

- It adopts PLC control and steeples frequency conversion speed regulation.
- The working processes such as unwinding, plastic forming, filling, batch number printing, indentation, punching and cutting are completed automatically by the program.
- It adopts human-machine interface device, which has simple operation.
- The filling has no dripping, bubbling, and overflowing.
- The parts contacting with medicine all adopt high quality stainless steel material, which meets with GMP standard.
- The main pneumatic and electrical components adopt imported brand.
- It adopts self-control filling system of electronic peristaltic pump and mechanical filling, which have accurate metering with small error.

### **Application**

It is suitable for oral liquid, liquid, pesticide, perfume, cosmetics, fruit pulp, food, etc.

### **Main technical parameter**

Max. forming depth	12mm
Punch frequency	0-25
Packing material	PVC/PE, PET/PE (0.2-0.4) ×140mm
Filling volume	1-50ml
Toal power supply power	7KW
Voltage	220-380V/50Hz
Machine weight	900Kg
Overall dimension (L*W*H)	2300×850×1400(mm)