



Automatic High Speed Wet Glue Labeling Machine



Pack Well is Gum Labeling Machine automatically paste labels on round container of glass, plastic, aluminum, pet, cardboard container and wrap-around labels in the vertical position by using cold glue. This machine is rigid, versatile and engineered for reliability and enhance operational efficiency in addition, it has several exclusive features which offer additional advantages.

Operation:

The round containers positioned & curate spacing between two containers by the roller spacing device for wrap-around operation at the operation at the labeling point, an electronics product sensor sense container & relies a label from self adhesive label roll. If machine is equipped with batch printing device in that case batch printing device prints the batch no. & other matter on label during label is stationary means time between sensing of two label. The sensed round container moves on conveyor sticker label at labeling point wrapped around to container. Then the labeled container moves further through a rubber pressing belt & stationary rubber pad that ensures neat & perfect fixing of label.

Specifications:

Model		Horizontal Sticker Labeling Machine
Direction of Movement		Left to Right
Output/Hour*		3600 to 9000 Nos.
Electrical Specification**	Main Motor	0.75 HP, 415 Volts, 50 Hz
	Vacuum Pump	0.5 HP, 415 Volts, 50 Hz
Height of Conveyor**		860 mm to 910 mm
Machine Dimensions**		3010 mm (L) x 1060 mm (W) x 1170 (H) mm
Case Dimensions		3250 mm (L) x 1250 mm (W) x 1200 mm
Net Weight		550 Kgs.
Gross Weight		900 Kgs.
Change parts required		(A) Container: Feed Worm.
		(B) Label: Label Muster, Upper – Lower Plate, Pusher Plate.
Input Specification		
Label	Length**	20 mm to 140 mm ***
Specification	Width **	16 to 90 mm***
	Thickness	65 to 70 GSM (The Direction of Grains of the label must always be parallel to the containers axis. The paper should be flexible)
Container Size**	Round Shape	Ø 16 mm to Ø 100 mm ***
		Respectively height 40 mm to 240 mm***
		(Height option for `other bottle height available)
Wet Glue	Glass/Plastic/PET etc	As per recommended in user manual.