

www.saintyco.com

Suppository Filling and Sealing Machine



CATALOGUE

Automatic Suppository Filling and Sealing Machine

SFFS-15P Type High Productive Automation Machine for the Production of Suppository is a new product developed by means of digesting and absorbing foreign advanced technology and integrating with suppository production practice home and abroad. It is the highest automatic suppository equipment and yield the greatest in the country today. Production up to 30,000 granulations/hour.

The unit consists of four parts:

- 1. High-speed band-making machine,
- 2. High-speed infusion machine,
- 3. High-speed freezer.
- 4. High-speed sealing machine.



SFFS-15P

Features:

- Up to 30,000 granulations/hour
- The adoption of PLC programmable control and human-computer interface operation the unit is simple to operate and with high automaticity.
- With the function of automatic deviation rectification the characters' position can be controlled as you like. The suppositories have the neat and good appearance.
- With the function of detecting collapse, infused quantity, the liquid level of the charging basket.
- The infusion is adopted the servo motor system exactly adjusting the infusing quantity with menu-memory-function and simple to change the specifications.
- The adoption of insert-type straight line infusion mechanism has the advantages of correct location, no drop medicine, and no adhesion phenomenon.
- Cooling protection shut down, the band comes out continuously without end breaking and low waste rate.
- Not infusing the wastes, auto-drill, and automatic rejection of them at the end of the machine.
- Interlock protection, intelligent alarm, and safety assurance.
- Continuous band-making and sealing and the shearing numbers can be set at will.



High precise automatic measuring adjustment equipment




Continuous low temperature cooling shaping



High quality continuous sealing





SFFS-15P
18,000-30,000 granulations/hour
1-5ml per granulation
(also can be made special qualification)
±2%
Bullet, torpedo, and other special shape
Semi-synthesis fatty acid glyceride gelatin,
polyethylene glycol, etc.
PVC,PVC + PE,PVC + PVDC + PE
(Height: 56-58 mm Thickness: 0.15 ± 0.01 mm)
50L
17.4mm
2,000mm
three-phase AC 380V
17kW
0.55-0.65MPa
1.0m³/min
480L/h (used in circle)
7400 x 2100x 2400mm
3000kg

SaintyCo also offer:

Encapsulation Solutions

Tablet Compression Solutions

Coating Systems

Cartoning Systems

Blister Packing Solutions

