



SPZ 400/32 ampoule tunnel sterilization dryer



Our ampoule tunnel sterilization dryer is mainly used on the injection linked production line of pharmaceutical factories. It is suitable for continuous drying, sterilizing and pyrogen removing of the washed ampoule or big/small glass medicine bottle.

Features:

- Using heating of “hot air laminar flow”, it achieves constant and even heating
- Short sterilization time, good sterilization effect
- High production capacity

Technical Parameters:

Model	SPZ 400/32	ASMR 600/43
Production Capability	7000-20000 bottle/hour	11000-30000 bottle/hour
Tunnel Air Cleaning Level	100 class (USA standard 209E)	
Power	Machine power: 36.59kw	Machine power: 47.39kw
	Elec. Heating power:32.4kw	Elec. Heating power: 43.2kw
Power supply	380V 50Hz (3-phase 5-line)	
Noise Of Whole Machine	Less than 80 dB(A)	
Max. Working Temperature	350°C	
Bottle Outlet Temperature	Lower than room temperature+15°C	
Packing Size (mm)	3150x1400x2350	3150x1550x2350
Packing Weight	2100kg	2200kg