

AL-Cap Sealing Machine DAC-3000



- High stability from the stable flow of bottles.
- Low noise and smooth transportation.
- Easy repair and maintenance.
- Minimized error rate by sealing with the sealing head unit specially produced.
- Adjustment of the sealing head unit's vertical position available with the digital gauge.
- Convenient and swift part changing.
- Control of the entire production process with the interlock.

Entrance and discharge of receptacles/feeding of caps

Sealing by the rotation of the sealing axis

Touch Screen



Technical Data:

Description		Model		
		DAC-1000	DAC-2000	DAC-3000
Output (Vials/Hour): 10ml		100 ~ 120	200 ~ 220	300
Number of Sealing Head		1 pcs	8 pcs	12 pcs
Electricity Consumption	Standard Voltage	AC 220/380V, 50/60Hz		
	Installed Power	2.0 kw		4.0 kw
Dimension	Length	960 mm	1360 mm	2460 mm
	Width	920 mm	900 mm	1200 mm
	Hight	1900 mm	1960 mm	2000 mm