



JMP08 Powder Pulverize



Application

It is specially used for pulverizing those dry and brittle material in cosmetic, chemical, pharmacy industries



Features

- It adopts rotary multi-hammer to hammer the powder material, which makes powder is sheared off, scraped, scattered and pass through the mesh in high speed to achieve the requested fineness.
- The structure is simple and precision, small footprint and easy to clean.
- Due to the huge heat caused during pulverizing, the machine has water cooling device to prevent some of material from thermal anaphylaxis. It will release heat out of machine body by water-circulation and keep temperature at a suitable degree inside.
- Comparing with general pulverize, it adopts screw feeder to put raw material into the rotating crusher. Under high-speed revolution, special crush mechanism can get better homogeneity and emulsification after spraying the oil. It can avoid oil spot at the surface of powder cake and make sure its softness.

Technical Parameters

Model	JMP08
Capacity	20-50kgs/h
Rotary Speed	7200RPM
Material Inlet	Screw feeding, speed is adjustable
Hammer	8PCS
Crushing Motor	7.5kw