

CY-102 Capsule Polishing Machine



This polishing machine is used after capsules are for cleaning the powder attached on the capsules surface, through mechanically rotating brush and attraction of vacuum to take out the external powder of capsules.

Features:

- All stainless shell, hopper and surface plate meeting G.M.P requirements.
- Easy to operate, excellent performance and lesser maintenance.
- Gentle, Non-Scratch brush polishing.
- The inclined position of polishing barrel and brush gives highet efficiency.
- High capacity & efficiency.
- Instant faction (control of behave).

Applicability:

Applicable to all size of capsules #00-0-1-2-3-4-5

TECHNICAL DATA	
Capacity	Max.400.000 Pcs/Hr
Power Supply	Ac110/220v 50/60Hz
Power Consumption	1/4Hp
PACKING DATA	
Measurement	120x50x120cm (LxWxH)
Packing Size	150x55x80cm (LxWxH)
Net Weight Gross Weight	50kgs / 95kgs