

Best Softgel Encapsulation Machine SIN-series



Softgel Encapsulation Machine compared with similar products on the market, it has incomparable outstanding advantages in terms of performance, quality, appearance, etc., and enjoys a good reputation in the market. Sinoped summarizes the defects of past products, and continuously improves them. The specifications of Softgel Encapsulation Machine can be customized according to your needs.

Production Process

The working principles: put the oil, gelatin-insoluble liquid, paste, plaster inject into between two gelatin skin quantificational, through the two roller dies and press and cutting into various shape soft capsules, The product is widely used in pharmaceutical, cosmetic, health food and pesticide etc.

Technical Parameters

Model	SIN-100	SIN-150
Rolling die speed	0-5r/min	0-5r/min
Rolling die size	64*100mm	103*100mm
Capacity	18000 pcs/h	380V50HZ
Power	380V50HZ	380V50HZ
Dimension	1300*550*1350(h)mm	1680*600*1550(h)mm

Model	SIN-15(paintball)	SIN-250
Rolling die speed	0-5r/min	0-5r/min
Rolling die size	64*100mm	150*250mm
Capacity	10800 pcs/h	100,000 pcs/h
Power	380V50HZ	380V50HZ
Dimension	2110*1000*2000(h)mm	2110*1000*2000(h)mm