



## ZP5 Rotary Tablet Press



### Application

- Design of GMP.
- High quality all stainless steel constructions.
- Reliable safety sealing system and dust-proof system.
- High visibility isolated door to prevent cross contamination.
- Easily remove parts for quick machine's maintenance.

### Feature

All controllers and operating parts are well laid out. The frequency control device is used for electric speed regulation, which is convenient to operate, stable in rotation, safe and accurate. All transmissions are placed inside the machine to keep the parts clean. Equipped with overload protection device, it can automatically stop when the pressure is overloaded. This machine is equipped with an electromagnetic brake motor and other safety protection devices, which can be adjusted and operated during operation.

### Technical Parameters

Model	ZP 5
Dies (sets)	5
Max. Pressure (kn)	40
Max. Depth of fill (mm)	15
Max. dia. of tablet (mm)	12
Thickness of largest tablet (mm)	6
Production capacity (pc/h)	9000
Motor (kw)	1.5
Overall dimensions(mm)	400*580*1000
Net weight (kg)	310