



## *KW-106 Capsule & Tablet Inspection Machine*



KW-106 inspection machine is designed and used for inspecting capsule or tablet which is spotty, broken. Or not standard by vision through mechanically rotating the capsule over 360 degree or turning the tablet from one surface to the other surface. Inspection can be easily determined.

### **Features:**

- All stainless shell, body hopper, and guide meeting G.M.P. requirement.
- Feeding variable speed.
- Conveying belt is special, durable and easy to clean.
- No noise, no public hazard.
- Simple operation, maintenance, and convenient to use.
- Change guide from capsule to tablet within 10 minutes, vice versa.

### **Specifications:**

Applicable to all size of capsules, tablets, ball pills and all type of solid medication.

<b>PACKING DATA</b>	
<b>Measurement</b>	2065x380x1325mm(LxWxH)
<b>Net Weight</b>	150kgs
<b>Gross Weight</b>	220kgs
<b>TECHNICAL DATA</b>	
<b>Capacity Capsule</b>	Max 50,000 Pcs/Hr
<b>Capacity Tablet</b>	Max 70,000 Pcs/Hr
<b>Capsule</b>	1 Person
<b>Tablet</b>	2 Person
<b>Power Supply</b>	AC 110/220 50/60Hz
<b>Power Consumption</b>	1/4 HP