

## DJL-12A Electronic Counter



The equipment counts and fills medicine automatically.

Capsule, soft gels, normal tablets, special shape tablets, coating tablets, pills and most solid granules are fed from hopper to counters by quiver to prevent material breakage, through the high anti-dust sensor technology and adjustable baffles at the outlet of loader into the bottle.

High anti-dust sensor technology ensures counting works accurately with good stability in heavy dust conditions, while baffles control the filling speed of material.

### Application:

For capsule, soft gels, normal tablets, special shape tablets, coating tablets, pills and most solid granules. Suitable for filling in plastic bottle with square, round, flat-square and special shape bottle.

### Technical parameters:

Bottle Sensor	To detect bottle in conveyor
Dimension (L x W x H) mm A	1400x1400x1560
Dimension (L x W x H) mm B	1600x1600x1560
Weight (kg) A	220
Weight (kg) B	270
Working Range	lebih dari atau sama dengan 2 (adjustable)
Counting system	Nantong Hengli
Speed Control	T.W.T
Capacity (Bottle per minute)	20-40
Power Supply	220 V ; 50 Hz
Power Consumption	0.8