

SM-2 Automatic High-speed Cotton Inserters



The equipment adopts the high-precision photo electronic locating system to automatically break the cotton sliver and insert in the bottle to ensure accuracy of position.
Self-diagnose errors and stop working to make alarm at errors and missing bottles as well as change cotton sliver.
Adopt pneumatic cotton-inserting technology to avoid pollution of materials.

Technical Parameter:

Applicable	50-500ml, Inner diameter of the of bottle neck must be more than 22mm.
Applicable cottons	Medical grade coil cottons of diameter $\Phi 30$ (bulk), well-proportioned.
Capacity	60-100 bottles/minute
Power supply	220V/50Hz 0.9kw
Air supply	0.6Mpa, 20l/min
Size	1600*750*1400mm
Weight	200kg