

## **RGPL-0735A**

## 香水生产线



- It is equiped with air cleaning for bottles, quantitive filling, negative pressure filling, pump placing, lid rolling, jacket placing, capping, rejecting, labeling and end product collecting etc.
- Moulds move in circles, easy to change bottles; Stepping motor for quantitive filling, fast to adjust filling volume; Negative pressure device is used to fill in the same liquid level; Manipulator for pump placing and pre-rolling is applied to increase pump rolling rate;
- Elastic rolling head is to avoid the bottle body from damage.

Bottle Diameter ≤80mm Bottle Length ≤80mm Maximum filling 250ml

Power Supply 380/220V(Optional)

Compressed Air 0.6~0.8Mpa

Dimension 5800(L)×3400(W)×2000(H) mm