

## *KBG-W mini liquid filling machine*



KBG-W mini liquid filling machine can filling liquid into glass vial, it is used in pharmaceuticals, bio-chemicals, cosmetic and food industry. The machine use turn table to load and position the vial, reliable using, easy maintenance.

Integrated the mechanical and electrical technology, filling volume is control by computer, use the peristaltic pump to fill liquid, with high accuracy, easy cleaning, no liquid drop, no contamination, can filling different kind of liquid. It is advance mini liquid filling machine in domestic.

Use the vibration hopper to sort and load rubber stopper. Use the vacuum device to put on the stopper, reliable working, and easy regulation. Use the stainless steel part which contact with vial and liquid, no toxic and anti-corrosion. The table and machine frame is made of stainless steel plate, easy cleaning.

### **Main technical parameter:**

Filling station	1					
Filling range	0.1-0.5 ml	0.5-1 ml	1-2 ml	2-5 ml	5-10 ml	10-20 ml
Filling error	≤±3%	≤±2%	≤±1.5%	≤±1.5%	≤±1%	≤±1%
Productive capacity	30vial/min.					10 vial/min.
Vial breaking	≤0.2%					
Stopper missing	≤0.5%					
Vacuum degree	6.6×10 <sup>-2</sup> MPa vacuum consumption					
Outside dimension	900×460×900(mm)					
Weight	120kg					