



Ambalica Engineers

Bottle Liquid Filling Machines



The incoming dry bottles (sterilized and silicones) are fed through the in-feed turn table and suitably guided on the moving SS/Plastic slat conveyor belt at the required speed of the correct placement below filling unit. Bottles in a row are held by pneumatic stoppers at a time below the filling nozzles. During the stationary position, the set fill volume is delivered into bottles.

Technical Specifications:

Model	ABL-45	ABL-60	ABL-80	ABL-100	ABL-150
	(Semi Auto)				
No. of Heads/Syringes	2 Nos.	2 Nos.	4 Nos.	6 Nos.	8 Nos.
Output/Minute	10 to 40 bottles	25 to 60 Bottles	25 to 80 Bottles	80 to 120 Bottles	80 to 150 Bottles
Fill Size *	15ml to 500ml (With the help of change parts)				
Fill Accuracy	±1%				
Container Dia	20mm to 75mm				
Container Height	25mm to 170mm				