

KWH type outer bottle Cleaning Drier



Purpose and brief

This machine is the cleaning and drying equipment of the oral liquor assembly line after filling and sealing, which is used to clean and dry the outside of 5-20ml straight tube bottle and as opts the screw transportation. The bottles repeatedly washed with preaurized water and blow off the surface water with purified compressed air, and then transferred into the drying tunnel to dry in the appropriate temperature.

Main technique parameters

Production ability: 80~100 bottles/min
Applied bottle: 10~20ml straight tube bottle
Drying temperature: 120°C~140°C
Power supply: 380V 50Hz Three-phase four-wire
Power: ≤10Kw