

TXP General Washing Machine



This machine is decontamination equipment of glass bottle; it is used in all kinds of cleaning of heterogeneous bottle and round bottle. Uses parallel clamps the bottle turn over transmission, and clamps the bottle caterpillar tread spacing adjustability and the reliability; Each bottle can pass trough multi-channel returns the water used, the pure water and purification compressed air clean processing, achieves the ideal clean effect.

Technical Parameters

Production capacity	3600 - 7200 bottle/hour (I type)
	7200 - 12000 bottle/hour (II type)
Applied bottle	50 ml - 1000 ml, glass bottle or plastic bottle
Water to flow	0.5 - 1 m ³ /h, pressure: 0.2 - 0.3 MPa
Consumption of purification water	0.5 - 0.6 m ³ /h, pressure: 0.2 - 0.3 MPa
Consumption of compressed air	0.6 m ³ /h, pressure: 0.2 - 0.3 MPa
Power	3 KW
Power supply	AC,380V/50HZ 3 phase or customization
Overall size	2400(3000) x 1100 x 1600 mm