

SED-250RJ-I Fully Automatic Soft Gelatin Capsule Filling Machine



The encapsulation machine is the main device, together with the corresponding auxiliary equipment, component production line.

- for volume-production, increase the utilization ratio of gelatin;
- convey gelatin skin with a plane surface more steady running condition;
- oil-saving

Feature:

1. Capsule package rate is up to 98%.
2. The gelatin ribbon is lubricated by fine oil supply technology in order to lower the consumption of lubrication oil. The ribbon is lubricated by vegetable oil, so the capsules produced is free of wash.
3. High quality capsule deferent equipment adopts food conveyer belt authorized by American FDA, without poison and adhibition and easy to clean.
4. Optimized designed mould is made of high quality aviation alloy material by high precision numerical control process to insure the mould's service life.
5. Advanced process and assembly technics make the complete appliance quality stabilization, high working rate, and good shape pill.

Technical Parameters

Model	SED-250RJ-I
Roller die rated speed	0~5r/min
Roller die size	Φ150×250mm
Single piston feeding volume	0~2ml
Power supply	380V 50Hz
Total power	7.55kw
Noise	<75dBA
Dimension	2420×1200×2200mm