



Automatic Pharmaceutical Vial/Bottle Filling Machine GTI-2



Brief introduction

- * This production line suitable for Vial washing, Dry and sterilization, Powder filling and stoppering, Capping(roll); Widely use for drugs, Biologies agents, Health products etc.
- * Production line composed by QCL Vertical ultrasonic washing machine RHX Hot air circulation tunnel oven, SHFJ Powder filling and stoppering machine, ZG Capping(roll) machine; Can be connected for production line or stand-alone.
- * According to customer technological requirements configuration can satisfy different specifications and production speed.

Technical Parameters:

Product Model	SHFJ-2	SHFJ-4	SHFJ-6
Applicable specification	0.1-3g	0.1-3g	0.1-3g
Production speed	60-100 (b/m)	120-200 (b/m)	200-300 (b/m)
Filling error	±3%	±3%	±3%
Water pressure and water consumption	0.25-0.35mpa,0.5~5m7h	0.25-0.35mpa,0.5~5m7h	0.25-0.35mpa,0.5~8m7h
Power supply	380/220v,45KW	380/220V.85KW	380/220v,85KW
Purify compressed air pressure and air consumption	0.6-0.8mpa,5~15m7h	0.6-0.8mpa,30-45m7h	0.6-0.8mpa.30-45m3/h
Exhaust volume	2800m7h	3200m3/h	3200m7h
Weight	4000KG	8000KG	12000KG
Dimensions	10000 x 1800 x 1800mm	12000 x 12500 x2400mm	12000 x2500 x2400mm