

Auger DPT



Independent drive through motor, Auger exchangeable implements, Auger diameter from 10 mm up to 80 mm, Ready to receive signals of weight correction from a checkweigher, Independent stirring rods, Hopper level in order to control the devices of the product supply to the dosing unit.

Resolution 1 gram

Tolerance +/- 0,5%

Optional Equipment Additional auger implements, Clapet closure to avoid leakage of product, Unit for weighing product

USAGE

- Powder Product

WIDTH	HEIGHT	LENGTH	WEIGHT	POWER CONSUMPTION
750 M/M	1200 M/M	1465 M/M	12 KG	none