

## Capsule Polishing Machine



Stepless speed control is used in capsule polishing machine. As deal equipment for the production of capsules in the pharmaceutical industry, this product can be used to polish, clean and eliminate dust on the tablets, thus improving the surface finish and making drugs meeting hygienic standards. All the spare parts which may come into contact with drugs are made of high quality stainless steel, so they are resistant to rust corrosion. In compliance with GMP standards, this product can create a clean and hygienic environment for pharmaceutical packaging process.

### Detailed Specifications

Productivity	7000 pcs/min
Product range	Capsule or tablet
Power of motor	180W 220V
Dimension	1310x550x110mm
Weight	50kg