



## ***JMJ-2 / JMJ-2A Capsule Polishing Machine***



### **Feature:**

1. Small size, good looking , adjustable height and angles. It can be connected to any types of capsule filling machines. Timely polishing while producing is realized to raise the polishing quality and efficiency.
2. It can automatically sort out capsules with low weight, empty body, scrap and loose piece to meet GMP standard.
3. High quality stainless steel is used inside the medicine- polishing chamber. Quick connecting parts are also adopted to dismount the equipment more easily and to clean more thoroughly.

### **Technical Data**

Motor power	1000W
Extraction rate	1800mmH <sup>2</sup> O
Capacity	15 L
Gas flow	48 L/s
Rated voltage	220V