



DSM-P5 Plastic Ampoule Filling Machine



Oral liquid, liquid, pesticide, perfume, cosmetics and pulp food category, etc

Characteristic:

1. Controlled by PLC, the frequency conversion in finitely variable speeds.
2. All 6 processes from spreading roll, Ampoule bottle forming, filling, sealing the end, printing serial numbers, cutting the end, cutting apart, controlled by programming.
3. The computer human interface has simple and clear operation.
4. The filling head don't drop. Leak, riding bubbled and spill over.
5. All are made of high-quality stainless steel, accord with the standard GMP.
6. Mostly pneumatic components and Wirings adopt inward fittings.
7. Automatic and mechanical bottling, precise calculation and limited deflection.
8. Usage: Oral liquid, liquid, pesticide, perfume, cosmetics, etc.

Technical parameter:

Max forming depth	12mm
Cutting frequency	0-50 time 2 filling head
	0-100 time 5 filling head
Packing material	PVC/PE(0.2-0.4)X120mm
Capacity	2-25ml/Ampoule
Power	3.5Kw
Voltage	220/380V/50Hz
Whole machine's weight	350Kg
Outer size L x W x H(mm)	1800x800x1400(mm)