

## *DHC-250Z Medical Capsule/Tablet Blister Packing and Cartoning Packaging Line*



The packaging line can be widely used for packing different size of capsule, tablet and solid products (Alu-PVC/Alu-Alu) blister packing and cartoning. Can be connected with weighing machine, strapping machine, carton packer and other equipment, thus formed a complete automatic packaging production line.

- Machine with GMP and cGMP standard, adopts PLC control system, servo motor drive control.
- All components that contact with medical are made of high anti-corrosive SS316.
- Equipped Camera detection, lack of material testing, to ensure the passing rate of finished products.
- Uses the safety cover protection devices to ensure operator safety.
- Machine can be separated to some parts, order easy move into the elevator and clean room.
- Optional: Aluminum foil online printing system (HAPA Aluminum foil printer).

### **Technical parameters**

Max Output :	≤100 cartons/min
Max Forming area and depth:	245×100×35mm
Leaflet size :	(100-260) × (100-170) mm
Carton material:	250-350g/m <sup>2</sup>
Carton Size:	(60-230) × (20-140) × (14-80) mm
Leaflet material:	50-70g/m <sup>2</sup>
Air compressor	0.6-0.8/Mpa≥0.8m <sup>3</sup> /min
Power	380V 50HZ 8Kw(220V, 60Hz)
Weight	5000kg