




## ***Pellet coating machine BP-600***



In order to adapt to the development of domestic pharmaceutical industry and carry out GMP standard. This machine is improved on the basis of original water chestnut mode coating machine.

The machine is mainly used for coating and polishing the shaped pellet and micro granule in pharmaceutical industry, it is also suitable for food industry for candy coating, used for pill manufacturing or coating. The sugarcoated tablets have bright and smooth surfaces after being coating polished, which protects the tablet core from being oxidized and deteriorated, being affected with damp or volatilizing. It also covers the peculiar smell of tablet core, makes it easy for distinguishing and dissolving in human stomach intestine system.

The machine is simple to operate, convenient for maintaining, low cost, and is the ideal equipment for coating in pharmaceutical industry.

### **Technical Parameters:**

Dia. of the oven pot	600mm	800mm	1000mm	1250mm
Production capacity (kg/time)	10-15kg/time	30-50kg/time	50-70kg/time	80-150kg/time
Rotary speed of main engine	0-40(r/min)	0-32(r/min )	0-32(r/min )	0-28(r/min)
Power of main main engine	0.75kw	1.1kw	1.5kw	2.2kw