

SGKGZ-4/-8/-12 Oral Liquid Drying Filling and Sealing



This production line suitable for 5-25ml tube-type bottle oral liquid washing, drying, filling and capping (Roll). Production line composed by SGLCX Vertical ultrasonic wave washing machine, SGRHX Hot air circulation tunnel oven, SGKGZ Oral liquid filling capping (roll) machine. Can use production line or stand-alone. The technological process: Mesh belt into bottle, Ultrasonic wave washing, Three times water and air, clean bottle inside and outside, Dryand sterilization, Filling and capping(roll);

Product parameter

Product No	SGKGZ-4	SGKGZ-12	SGKGZ-16
Application Specification	5-25ml	5-25ml	5-25ml
Production speed	60-80(b/m)	150-220(b/m)	300-350(b/m)
Filling error	± 1-2%	± 1-2%	± 1-2%
Water pressure and water consumption	0.25-0.35MPa,0.5m ³ /h	0.25-0.35MPa,1.5m ³ /h	0.25-0.35MPa,0.5m ³ /h
Power supply	380/220V,8KW	380/220V,42KW	380/220V ,80KW
Punfy compressedair pressure and air consumption	0.3-0.5MPa, 10m ³ /h	0.3-0.5MPa,5-15m ³ /h	0.3-0.5MPa,30-45m ³ /h
Exhaust volume	/	2600m ³ /h	3200m ³ /h
Weight	650KG	3000KG	7500KG
Dimensions	4000×1300×1500mm	11000×1800 x 2000mm	12000×2500×2400