

## **Drum Ultrasonic Washing Machine**



The drum ultrasonic washing machine is a kind of cleaning equipment for penicillin bottles and oral liquid bottles. Rotary drum structure is designed for it, and bottles need to be cleaned several times in this drum ultrasonic washing machine. First, they are washed by ultrasonic waves. Then they will be cleaned by running water, distilled water and purified compressed air in turn.

## Features:

- 1. Stable operation, reliable performance, and excellent washing effects.
- 2. The transparency of bottles can meet related standards only after washing by ultrasonic waves and pressure water.
- 3. One-button control design makes its operation quite easy.
- 4. Convenient to install and maintain.

## **Main Parameters:**

Production Capacity	3600~6000 bottle/hour
Bottle Size	30ml-50ml, 50-100ml, 200-500ml glass bottle
Ultrasonic Power	1kw
Electric Supply	380V/50hz, 3phase
Power	3kw
Size	2000×1100×1500mm