

TXP universal type bottle washing machine



Purpose and brief:

This machine is the glass jar decontaminating unit, is suitable in each kind of heterogeneous type or the garden shape jar clean. Uses parallel clamps the bottle turn over transmission the new technology, carries on the jar the transportation, also clamps the bottle caterpillar tread spacing to be possible to move, thus, this machine and tools have the very good compatibility and the reliability; Each jar all can pass through multichannel returns to the water used, the pure water and purification compressed air clean processing, achieves the ideal clean effect. This machine to replace the bottle, bottle clamping band spacing can be adjusted only, without replacing any mold.

Main technique parameters:

Reduction ability: 60~120 bottles/Minute (I)

120~200 bottles/Minute (II)

Applied bottle: 50~1000ml

Sales commission discharge of water: 0.5~1m³/H

Pressure: 0.2~0.3MPa

Purification water consumption quantity: 0.5~0.6m³/H

Pressure: 0.2~0.3MPa

Purification compressed air consumption quantity: 0.6m³/Min

Pressure: 0.2~0.3MPa

Power supply: 380V 50Hz Three-phase four-wire

Power: 2Kw