


DPP-250 Plate Type Packaging Machine



This machine uses forming material to contact heating, press forming (thickened ALU-ALU), plank pose sealing advanced function, according to GMP standard. Suitable for medicine (tablet, capsule, ampoules, cylindrical vials, pill, suppository), food, industry, cosmetic and medicine device etc.

Performance Advantage:

1. It's easy to change mould, ALU-PVC material, press forming. It is rational design. Avoid product deform and be broken by long time baking when machine stop.
2. It can make batch number and perforation, clear and beautiful. Enough filling platform is suitable for packing regular and irregular tablets, capsules, food etc. Production is straight and bubble cap plump.

Main Technical Data

Model	DPP-250
PVC sheet	Thickness:0.2-0.3 width:160-250
	Max outside diameter:Φ500
Max aluminum foil	Thickness:0.02 width:160-250
	Max outside diameter:Φ300
Max stepping distance(mm)	165
Max forming area(mm)	165×250
Max forming depth(mm)	ALU-PVC : 24 (Special : 30)
	Double-ALU : 12

Cutting frequency(Min)	20-40 cycles
Air consumption(min)	ALU-PVC : 35L
	Double-ALU : 10L
Water consumption(min)	1L/min
Air pressure	0.6~0.8 Mpa
Power	220/380V 50HZ 12KW
Size L×W×H (mm)	3900×1300×1900
Net weight (kg)	2200
Re : No additional information noted if there are any changed caused by the technical development.	