


CXM-GFT Auto Syrup Liquid Filling Machine



1. The parts which contact liquid are SUS316L stainless steel and others are SUS304 stainless steel
2. Including feeder turntable, effective cost/space saving
3. It has intuitive and convenient operation, measuring accurate, positioning precision
4. Fully in accordance with the GMP standard production and passed CE certification
5. Optional Siemens Touch screen/PLC
6. No bottle no filling (optional)

Technical Parameters

| | |
|-----------------------|--|
| Applied Bottle | 50-500 ml (can be customized for 1000ml) |
| Productive Capacity | 10-30pcs/min 2 filling nozzles |
| | 20-40pcs/min 4 filling nozzles |
| | 30-50pcs/min 6 filling nozzles |
| | 60-80pcs/min 8 filling nozzles |
| | 80-100pcs/min 10 filling nozzles |
| | 100-120pcs/min 12 filling nozzles |
| Filling Tolerance | 0-2% |
| Qualified Stoppering | ≥99% |
| Qualified cap putting | ≥99% |
| Qualified capping | ≥99% |
| Power Supply | 380V ,50HZ |
| Power | 1.5KW |
| Net Weight | 600KG |
| Dimension | 2500(L)×1000(W)×1700(H)mm |