

CXP type ultrasonic bottle washing machine



Purpose and brief:

This machine is of vital or oral liquid bottle cleaning equipment, using drum structure, for the bottle tray for the bottle after bottle feeding, wheel, drum of intermittent feeding bottle, after ultrasonic water used to water (or water), distilled water and purified compressed air alternately flushing finished washing bottle. This machine has stable operation, reliable operation, good cleaning effect and other advantages.

Main technique parameters:

Production ability: 60~120 bottles/min
Applied bottle: 2~100ml glass bottle
Ultrasonic power: 1Kw
Power supply: 380V 50Hz Three-phase four-wire
Power: 3Kw